


**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 60****Order data**

Order number	GG5779 60
GTIN	4062406201784
Item class	GGN

**Description****Version:**

Dust-repellent coating prevents premature clogging. The back is covered with hook and loop backing.

Velour-backed abrasive disc with semi-open distribution, aluminium oxide (A).

Corresponds to 567790.

**Application:**

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

**Technical description**

Disc Ø	150 mm
Grit	60
Contents	500

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm
Number of dust extraction holes	15
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

## Accessories

Multi-hole PU backing pad External Ø 147 mm	567990 147
---	------------

PU hook and loop backing pad Multiple holes Outer Ø 150 mm	567887 150
PU hook and loop backing pad External Ø 150 mm	567885 150
Velour-backed abrasive disc (A) 15 holes Grit 60	567790 60