

**Cordless drill / driver, Type: GSR1235****Order data**

Order number	070241 GSR1235
GTIN	3165140953719
Item class	03B

Description**Version:**

Bosch cordless drill / driver

- **Compact, powerful 12 V cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Top power-weight ratio with up to 20 Nm torque for powerful screwdriving, yet low weight and very short head 163 mm.

Long service life thanks to **brushless EC motor**.

Supplied with:

Supplied with charger and L-BOXX.

Note:

Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

Battery voltage	12 V
-----------------	------

suitable battery - supplier / battery type / voltage	Bosch 12 V
maximum twist drill size Ø in wood	19 mm
Quick-clamping chuck range	0 - 10 mm
maximum vibration to EN	<1.9 m/s ²
Speed range 1st speed	0 - 400 min ⁻¹
Number of rechargeable batteries contained	2
maximum torque soft	15 Nm
Speed range 2nd speed	0 - 1750 min ⁻¹
maximum twist drill size Ø in steel	10 mm
Battery capacity	3 Ah
Manufacturer's designation	GSR 12V-35
Motor design	Brushless motor
typical application	Strong
Weight	0.8 kg
Packaging	Modular case (L-Boxx)
maximum torque hard	30 Nm
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Drill/driver
USP1	12V
USP2	Brushless motor, in L-Boxx

Accessories

Battery charger Type GAL1240	073866 GAL1240
Li-ion battery Battery type, battery voltage B12 V	073855 B12