

## Working platforms for fork-lift trucks, Type: 1040X835



### Order data

Order number	919981 1040X835
GTIN	4052462053540
Item class	94B

### Description

#### Version:

Sturdy steel hollow-section construction of round sections with all-round railings. Rear wall of mesh and non-slip work platform. Can be lifted by fork-lift truck at the wide side. Insertion pins prevent the platform slipping off the forks. With galvanised tool storage tray.

Base area 740×740 mm.

#### Application:

For safe working on repair and maintenance tasks on high parts of buildings, ceiling lights etc.

#### Standard:

TÜV geprüft, entsprechend der DGUV (Deutsche gesetzliche Unfallversicherung).

#### Colour:

Yellow orange RAL 2000 **painted.**

#### Note:

Please comply with national regulations regarding use of working platforms with the fork-lift truck. Suitable working platforms for use in Austria (approved by TÜV Austria) and Belgium are available on request.

Height: 1900 mm

Width: 835 mm

Depth: 1040 mm

Footprint width: 740 mm

Footprint depth: 740 mm

Fork insertion slots dimension A: 200 mm

## Technical description

Weight	58 kg
Width	835 mm
Fork insertion slots dimension D	80 mm
Fork insertion slots dimension A	200 mm
Safe working load	240 kg
Depth	1040 mm
Fork-lift fork socket pitch B	280 mm
Height	1900 mm
Footprint width	740 mm
Footprint depth	740 mm
Type of product	Attachment for fork lift truck