

Garant

eco parting-off tool, neutral, Blade height h₅ / groove width w: 32/4,1 mm


Order data

Order number	273564 32/4,1
GTIN	4062406202798
Item class	21U

Description
Version:

With eco cooling directly to the cutting edge and additional flank face cooling.
With coolant transfer for toolholders from other manufacturers (e.g. EWS).

Application:

For deep grooves and parting off large diameters.

Suitable for:

Toolholder No. 273893; 273894; 274095; 274097 or No. 319132 – 319133 (VDI toolholder).

Spare part:

Blanking screw No. 279828 size 2.

Sealing disc No. 279830 size 1.

Attention:

Please order the assembly key No. 279940 separately.

Technical description

for maximum workpiece Ø	110 mm
Series	Eco
Blade height h ₅	32 mm
Groove width w	4.1 mm
Overall length L	150 mm
Application type	neutral
Through-coolant	yes

System key	yes
axial grooving possible	no
Type of product	Parting-off tool