

**Garant**

eco parting-off tool, neutral, Blade height  $h_5$  / groove width  $w$ : 32/3,1 mm


**Order data**

Order number	273564 32/3,1
GTIN	4062406202781
Item class	21U

**Description**
**Version:**

With eco cooling directly to the cutting edge and additional flank face cooling.  
With coolant transfer for toolholders from other manufacturers (e.g. EWS).

**Application:**

For deep grooves and parting off large diameters.

**Suitable for:**

Toolholder No. 273893; 273894; 274095; 274097 or No. 319132 – 319133 (VDI toolholder).

**Spare part:**

Blanking screw No. 279828 size 2.

Sealing disc No. 279830 size 1.

**Attention:**

Please order the assembly key No. 279940 separately.

**Technical description**

Series	Eco
Groove width $w$	3.1 mm
Blade height $h_5$	32 mm
for maximum workpiece $\varnothing$	100 mm
Overall length $L$	150 mm
Application type	neutral
Through-coolant	yes

System key	yes
axial grooving possible	no
Type of product	Parting-off tool