



## Dynafile® pneumatic belt linisher, Type: 14000



### Order data

Order number	079551 14000
GTIN	616026140004
Item class	03R

### Description

#### Version:

Versatile machines with **adjustable linishing belt guides, exactly true-running belts**, and with an exchangeable **contact arm** allowing the use of contact wheel or side face. The composite linishing belt coating enables **quick** and **easy change of the linishing belt**. The **linishing belt** cooling via the exhaust air prolongs the working life of the belts. Adjustable handle **Dynafile®**, sturdy general-purpose linishing machine.

#### Application:

For abrading, deburring, blending, finishing and polishing, ideal also for flexible access to difficult places.

#### Supplied with:

Including the necessary coupling adaptors. 1 contact arm, linishing belt 13 × 610 mm.

#### Note:

Other contact arm versions for Dynafile® from No. 079559 available on request or in our eShop.

### Technical description

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Tape width	3–4; 6; 13 mm
Operating noise	77 dB(A)
maximum air consumption	876 l/min
Manufacturer's designation	Dynafile
Weight	1.4 kg

Output power	379 W
maximum speed	20000 min <sup>-1</sup>
Model range	Dynafile
Band length	610 mm
Compressed air connection	1/4 in
Connection thread	NPT
Packaging	Carrying case
Type of product	Linishing machine

---

## Accessories

Contact arm for Dynafile® Type 11218	079559 11218
Contact arm for Dynafile® Type 11219	079559 11219
Contact arm for Dynafile® Type 11231	079559 11231
Contact arm for Dynafile® Type 11232	079559 11232
Contact arm for Dynafile® Type 11213	079559 11213
Contact arm for Dynafile® Type 11216	079559 11216