



Triangular socket key, for screws: M10



Order data

Order number	623505 M10
GTIN	4020772044398
Item class	63Q

Description

Version:

Precision steel tube, galvanised, with tommy bar.

Application:

For triangular head bolts to DIN 22424 and triangular nuts to DIN 22425.

Standard:

DIN 22417 A

Shaft length: 140 mm

Head height internal size F: 15.05 mm

Shank Ø: 20 mm

Technical description

Shaft length	140 mm
Head height internal size F	15.05 mm
Shank Ø	20 mm
for screws	M10
Type	22417A

Type of product

Socket spanner