



Triangular socket key, for screws: M12



Order data

| | |
|--------------|---------------|
| Order number | 623505 M12 |
| GTIN | 4020772044404 |
| Item class | 63Q |

Description

Version:

Precision steel tube, galvanised, with tommy bar.

Application:

For triangular head bolts to DIN 22424 and triangular nuts to DIN 22425.

Standard:**DIN 22417 A**

Shaft length: 160 mm

Head height internal size F: 16.55 mm

Shank Ø: 20 mm

Technical description

| | |
|---|----------|
| Shank Ø | 20 mm |
| Shaft length | 160 mm |
| Head height internal size F for screws | 16.55 mm |
| | M12 |
| Type | 22417A |

Type of product

Socket spanner