

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 8/06mm**

**Order data**

Order number	260015 8/06
GTIN	4045197797582
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	8 mm
Head length L <sub>1</sub>	8 mm
Overall length L	150 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	SCACR/L 0808M06
Shank size	8 mm
Insert size	6 mm
Pack of insert screws	269021 1
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500