

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 8/07mm**

**Order data**

Order number	260298 8/07
GTIN	4045197797841
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
ISO code toolholder	SDACR/L 0808M07
Insert size	7 mm
Shank size	8 mm
Overall length L	150 mm
Functional width L <sub>4</sub>	8 mm
Pack of insert screws	269021 1
Head length L <sub>1</sub>	12.7 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 1	269021 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500