

Garant**Screw-on toolholder, right-hand, Shank / insert size: 10/07mm****Order data**

Order number	260298 10/07
GTIN	4045197797858
Item class	21T

Technical description

Shank size	10 mm
Insert size	7 mm
Head length L ₁	15 mm
Pack of insert screws	269021 1
Overall length L	150 mm
Functional width L ₄	10 mm
ISO code toolholder	SDACR/L 1010M07
suitable indexable insert	DC.. 0702..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500