

**Garant****Screw-on toolholder, left-hand, Shank / insert size: 10/07mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 260299 10/07  |
| GTIN         | 4045197797919 |
| Item class   | 21T           |

**Technical description**

|                                 |                               |
|---------------------------------|-------------------------------|
| Insert size                     | 7 mm                          |
| Pack of insert screws           | 269021 1                      |
| Functional width L <sub>4</sub> | 10 mm                         |
| suitable indexable insert       | DC.. 0702..                   |
| ISO code toolholder             | SDACR/L 1010M07               |
| Shank size                      | 10 mm                         |
| Overall length L                | 150 mm                        |
| Head length L <sub>1</sub>      | 15 mm                         |
| Standard                        | Works standard                |
| Application type                | left-hand                     |
| Through-coolant                 | no                            |
| Setting angle κ                 | 90 degrees                    |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |
| Type of product                 | Boring bar                    |

## Accessories

|  |            |
|--|------------|
| Insert screw Type 1  | 269021 1   |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7                             | 674248 TX7 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |