

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 8/11mm****Order data**

Order number	261314 8/11
GTIN	4045197798060
Item class	21T

**Technical description**

ISO code toolholder	SVACR/L 0808M11
suitable indexable insert	VC.. 1103..
Head length L <sub>1</sub>	26 mm
Functional width L <sub>4</sub>	8 mm
Overall length L	150 mm
Shank size	8 mm
Insert size	11 mm
Pack of insert screws	269021 1
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7
Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200