

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 12/16mm****Order data**

Order number	261314 12/16
GTIN	4045197798107
Item class	21T

**Technical description**

Head length L <sub>1</sub>	40 mm
Insert size	16 mm
Overall length L	150 mm
Shank size	12 mm
suitable indexable insert	VC.. 1604..
Functional width L <sub>4</sub>	12 mm
Pack of insert screws	269021 2
ISO code toolholder	SVACR/L 1212M16
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500