

Garant**Screw-on toolholder, left-hand, Shank / insert size: 8/11 mm****Order data**

Order number	261315 8/11
GTIN	4045197798121
Item class	21T

Technical description

Shank size	8 mm
ISO code toolholder	SVACR/L 0808M11
Head length L ₁	26 mm
Insert size	11 mm
Pack of insert screws	269021 1
suitable indexable insert	VC.. 1103..
Overall length L	150 mm
Functional width L ₄	8 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7

674248 TX7

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200