

**Garant****Screw-on toolholder, left-hand, Shank / insert size: 16/11mm****Order data**

Order number	261315 16/11
GTIN	4045197798152
Item class	21T

**Technical description**

ISO code toolholder	SVACR/L 1616M11
Head length L <sub>1</sub>	26 mm
Shank size	16 mm
Overall length L	150 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269021 1
Functional width L <sub>4</sub>	16 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7

674248 TX7

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200