

BENNING**Multimeter, Manufacturer's designation: MM5-2****Order data**

Order number	473300 MM5-2
GTIN	4045197801272
Item class	47A

Description**Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Microampere measurement range for ionisation current measurement, continuity testing with buzzer and red LED for noisy environments.

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions. Rubber protective surround with magnetic hanger.

Wire temperature sensor.

Calibration: I3

Calibration: I7

Information displayed: 6000

Basic accuracy: 0.5 %

Continuity testing: yes

Diode testing: yes

Voltage sensor (non-contact): yes

Measurement process: TRUE RMS (AC)

Technical description

Resistance	0.1 Ω – 40 M Ω
Measurement process	TRUE RMS (AC)
Capacitance	0.01 nF – 1 mF
Information displayed	6000
Overvoltage category	CAT III 600 V
Overvoltage category	CAT IV 300 V
Calibration	I3
Calibration	I7
Frequency	0.01 Hz – 50 kHz
Voltage sensor (non-contact)	yes
DC voltage	0.1 mV – 600 V
Diode testing	yes
AC voltage	0.1 mV – 600 V
DC current	0.1 μ A – 10 A
AC current	1 mA – 10 A
Basic accuracy	0.5 %
Memory function	HOLD
Memory function	Pmin / Pmax
Continuity testing	yes
Temperature	-40 - 400 $^{\circ}$ C
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

Services

Labellinglaser-etched Type	018940
CalibrationTemperature sensor with / without display Type A	027520 A
DAkkS calibrationTemperature sensor with / without display Type A	027540 A
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3
CalibrationDigital multimeter Number of decimal places 3	027000 3

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------