



Power clamp adjustable long, Type: 1



Order data

| | |
|--------------|---------------|
| Order number | 370091 1 |
| GTIN | 4020772004644 |
| Item class | 35A |

Description

Version:

- Clamping force 30 or 49 kN with tightening torque of approx. 100 Nm.
- Forged clamping element of alloy heat-treatable steel, black galvanised.
- Steplessly adjustable height and length.
- Low installed height.

Supplied with:

- Base element and carrier.
- T-nut DIN 508 with T-bolt strength class 12.9.

Optional extras:

Pressure pads No. 370095.

Technical description

| | |
|-----------------------|-------|
| T-slot width | 14 mm |
| Fastening screw G | M12 |
| Width across flats AF | 8 mm |
| with height element | no |

| | |
|--------------------------------|---------------|
| Clamping height h-H | 6 - 68 mm |
| B | 54 mm |
| B ₁ | 18 mm |
| A | 36 mm |
| A ₁ | 85 mm |
| Clamping force | 30 kN |
| Fastening screw G ₁ | M16 |
| L | 135 mm |
| Adjustment travel V | 13 - 110 mm |
| Type | 764CC |
| Type of product | Sliding clamp |

Accessories

| | |
|---------------------------------------|------------|
| Spacer element long for type 1/2 | 370093 1/2 |
| Pressure pad, stainless steel Type DG | 370095 DG |
| Pressure pad, stainless steel Type DR | 370095 DR |