



## Temperature and flow-rate measuring device, Type: 405I



### Order data

Order number	474186 405I
GTIN	4029547014260
Item class	47B

### Description

#### Version:

**Compact measuring devices optimised for the smartphone.** All measured data are transmitted directly to the free testo Smart Probes app (system requirement: iOS 8.3 or Android 4.3 or later / Bluetooth 4.0) and can be read by a mobile terminal, converted into a report and then sent out directly by e-mail.

- **Simultaneous display of up to 6 Smart Probes.**
- **Wireless reading of the measured values on your mobile device.**
- **Variations of the measured values can be displayed as a graph or as a table.**
- **Measured data reports can be supplemented by photos.**

Thermo-anemometer with smartphone operation. Measurement of air speed, volumetric flow and temperature. Easy configuration of dimension and geometry of the duct cross-section for determination of the volumetric flow. Telescopic tube with up to 400 mm extension.

#### Supplied with:

4 batteries No. 081561 LR3 and calibration certificate.

#### Note:

Further smart probes (thermometer, clamp thermometer, differential pressure measuring device and high-pressure measuring device) available on request.

### Technical description

Length	200 mm
Height	41 mm
Width	30 mm
Temperature measurement range	-20 - 60 °C
Airspeed measurement range	0 - 30 m/s
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	4
Power supply	Battery-powered
Type of product	Temperature and flow-rate measuring device

---

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------