



Temperature and flow-rate measuring device, Type: 410I



Order data

Order number	474186 410I
GTIN	4029547014277
Item class	47B

Description

Version:

Compact measuring devices optimised for the smartphone. All measured data are transmitted directly to the free testo Smart Probes app (system requirement: iOS 8.3 or Android 4.3 or later / Bluetooth 4.0) and can be read by a mobile terminal, converted into a report and then sent out directly by e-mail.

- **Simultaneous display of up to 6 Smart Probes.**
- **Wireless reading of the measured values on your mobile device.**
- **Variations of the measured values can be displayed as a graph or as a table.**
- **Measured data reports can be supplemented by photos.**

Thermo-anemometer with smartphone operation. Depiction of the volumetric flow at multiple outlets, for adjusting systems. Easy parameterisation of the outlet (dimension and geometry).

Supplied with:

4 batteries No. 081561 LR3 and calibration certificate.

Note:

Further smart probes (thermometer, clamp thermometer, differential pressure measuring device and high-pressure measuring device) available on request.

Technical description

Length	154 mm
Width	43 mm
Height	21 mm
Temperature measurement range	-20 - 60 °C
Airspeed measurement range	0.4 - 30 m/s
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	4
Power supply	Battery-powered
Type of product	Temperature and flow-rate measuring device

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------