

**Garant****Set of parallels, Length: 125mm****Order data**

Order number	366702 125
GTIN	4045197799265
Item class	31Z

**Description****Version:**

GARANT – **precision version**. Pairing tolerance  $\leq 0.004$  mm, width / height tolerance  $\leq 0.007$  mm, extremely precise flatness and rectangularity. Parallels stored in special plastic stand. Hardness: 60 HRC.

**Precision ground as pairs.****Application:**

In high precision work for parallel mounting of components in machine vices or jigs.

**Content:**

8×11; 8×16; 8×21; 8×26; 8×31; 8×36;  
10×13; 10×18; 10×23; 10×28; 10×33; 10×38;  
12×15; 12×20; 12×25; 12×30; 12×35; 12×40;  
14×17; 14×22; 14×27; 14×32; 14×37; 14×42

**Note:**

Sizes 125 – 200: In 1 mm increments, except 9 mm, all other dimensions achievable. See the spare parts list for spare holders. In 1 mm increments (except 9 mm), all other dimensions achievable.

**Technical description**

Length	125 mm
Number of strips	24 pair

Shape description	flat
Shape description	parallel
Shape description	rectangular
Type of product	Pairs of parallels

## Accessories

Single pair of parallels for 366702 / 6704 size 125 Width×height 12X40 mm	366711 12X40
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X35 mm	366711 12X35
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X20 mm	366711 12X20
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X23 mm	366711 10X23
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X25 mm	366711 12X25
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X37 mm	366711 14X37
Plastic stand for parallels Type 125-200	366701 125-200
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X22 mm	366711 14X22
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X32 mm	366711 14X32
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X33 mm	366711 10X33
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X16 mm	366711 8X16
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X11 mm	366711 8X11
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X36 mm	366711 8X36
	366711 14X42

Single pair of parallels for 366702 / 6704 size 125  
Width×height 14X42 mm

Single pair of parallels for 366702 / 6704 size 125  
Width×height 10X38 mm

366711 10X38

Single pair of parallels for 366702 / 6704 size 125  
Width×height 14X27 mm

366711 14X27

Single pair of parallels for 366702 / 6704 size 125  
Width×height 10X18 mm

366711 10X18

Single pair of parallels for 366702 / 6704 size 125  
Width×height 10X13 mm

366711 10X13

Single pair of parallels for 366702 / 6704 size 125  
Width×height 8X31 mm

366711 8X31

Single pair of parallels for 366702 / 6704 size 125  
Width×height 12X15 mm

366711 12X15

Single pair of parallels for 366702 / 6704 size 125  
Width×height 14X17 mm

366711 14X17

Single pair of parallels for 366702 / 6704 size 125  
Width×height 8X26 mm

366711 8X26

Single pair of parallels for 366702 / 6704 size 125  
Width×height 8X21 mm

366711 8X21

Single pair of parallels for 366702 / 6704 size 125  
Width×height 12X30 mm

366711 12X30

Single pair of parallels for 366702 / 6704 size 125  
Width×height 10X28 mm

366711 10X28