



## Clamping hook with collar M8, Type: 1



### Order data

Order number	370070 1
GTIN	2050001882530
Item class	37K

### Description

**Version:**

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

**Application:**

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

**Suitable for:**

Height element No. 370077.

### Technical description

Height $H_2$	14 mm
$F_{max.}$	7.9 kN
$H_1$	35 - 45 mm
Thread M	M8

Length 1	20 mm
Type	1
maximum torque	20 Nm
Type of product	Clamping hook