



Clamping hook with collar M8, Type: 2



Order data

Order number	370070 2
GTIN	2050001882677
Item class	37K

Description

Version:

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370077.

Technical description

Thread M	M8
Length 1	25 mm
F _{max.}	7.3 kN
Type	2

Height H ₂	14 mm
H ₁	35 - 45 mm
maximum torque	20 Nm
Type of product	Clamping hook