



Clamping hook with collar M8, Type: 3



Order data

Order number	370070 3
GTIN	2050001878472
Item class	37K

Description

Version:

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370077.

Technical description

Type	3
F _{max.}	6.7 kN
H ₁	35 - 45 mm
Length 1	30 mm

maximum torque	20 Nm
Height H ₂	14 mm
Thread M	M8
Type of product	Clamping hook