



Clamping hook with collar M8, Type: 4



Order data

Order number	370070 4
GTIN	2050001887719
Item class	37K

Description

Version:

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370077.

Technical description

Length 1	20 mm
H ₁	45 - 55 mm
Type	4
maximum torque	20 Nm

$F_{\max.}$	7.9 kN
Height H_2	14 mm
Thread M	M8
Type of product	Clamping hook