



Clamping hook with collar M8, Type: 5



Order data

Order number	370070 5
GTIN	2050001874979
Item class	37K

Description

Version:

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370077.

Technical description

Length 1	25 mm
F _{max.}	7.3 kN
maximum torque	20 Nm
Type	5

Thread M	M8
Height H ₂	14 mm
H ₁	45 - 55 mm
Type of product	Clamping hook