



## Clamping hook with collar M8, Type: 6



### Order data

Order number	370070 6
GTIN	2050001887856
Item class	37K

### Description

**Version:**

With countersunk screw.

Entirely of hardened and tempered steel; burnished.

**Application:**

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

**Suitable for:**

Height element No. 370077.

### Technical description

Type	M 8
Length 1	30 mm
Thread M	M8
Height H <sub>2</sub>	14 mm

$F_{\max.}$	6.7 kN
maximum torque	20 Nm
$H_1$	45 - 55 mm
Type of product	Clamping hook