

Garant
Lever lock toolholder, left-hand, Shank / insert size: 32/19mm

Order data

Order number	251113 32/19
GTIN	4045197801135
Item class	21T

Technical description

ISO code toolholder	PSSNR/L 3232P19
Shim	259031 38
Head length L ₁	40 mm
Overall length L	170 mm
Shim pins pack	259044 7
Functional width L ₄	40 mm
Lever screw	259018 13
Lever	259015 13
Shank size	32 mm
suitable indexable insert	SN.. 1906..
Insert size	19 mm
Shim punches pack	259047 5
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 7	259044 7
Lever screw Type 13	259018 13
Lever Type 13	259015 13
Shim Type 38	259031 38
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500