



Clamping hook with collar M12, Type: 1



Order data

Order number	370071 1
GTIN	2050001880437
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

Thread M	M12
H ₁	50 - 65 mm
Height H ₂	27 mm
Type	1
maximum torque	45 Nm

Length 1	40 mm
$F_{\max.}$	13.5 kN
Type of product	Clamping hook