



Clamping hook with collar M12, Type: 2



Order data

Order number	370071 2
GTIN	2050001880291
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

$F_{max.}$	12.6 kN
Thread M	M12
Height H_2	29 mm
H_1	50 - 65 mm
maximum torque	45 Nm

Type	2
Length 1	50 mm
Type of product	Clamping hook