



Clamping hook with collar M12, Type: 3



Order data

Order number	370071 3
GTIN	2050001877635
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

H ₁	50 - 65 mm
Length 1	60 mm
F _{max.}	11.7 kN
Thread M	M12
Type	3

maximum torque	45 Nm
Height H ₂	29 mm
Type of product	Clamping hook