



Clamping hook with collar M12, Type: 4



Order data

Order number	370071 4
GTIN	2050001886736
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

Height H_2	27 mm
H_1	65 - 80 mm
$F_{max.}$	13.5 kN
maximum torque	45 Nm
Length 1	40 mm

Thread M	M12
Type	4
Type of product	Clamping hook