



Clamping hook with collar M12, Type: 5



Order data

Order number	370071 5
GTIN	2050001886316
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

maximum torque	45 Nm
Thread M	M12
Height H ₂	29 mm
H ₁	65 - 80 mm
Type	5

Length 1	50 mm
$F_{\max.}$	12.6 kN
Type of product	Clamping hook