



Clamping hook with collar M12, Type: 6



Order data

Order number	370071 6
GTIN	2050001886453
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370078.

Technical description

Type	6
$F_{max.}$	11.7 kN
maximum torque	45 Nm
Length 1	60 mm
H_1	65 - 80 mm

Height H ₂	29 mm
Thread M	M12
Type of product	Clamping hook