



Clamping hook with collar M16, Type: 1



Order data

Order number	370072 1
GTIN	2050001887993
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370079.

Technical description

Thread M	M16
maximum torque	60 Nm
Height H ₂	36 mm
H ₁	50 - 65 mm
Length l	40 mm

$F_{\max.}$	13.4 kN
Type	1
Type of product	Clamping hook