



## Clamping hook with collar M16, Type: 2



### Order data

Order number	370072 2
GTIN	2050001880574
Item class	37K

### Description

**Version:**

Entirely of hardened and tempered steel; burnished.

**Application:**

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

**Suitable for:**

Height element No. 370079.

### Technical description

Thread M	M16
Height H <sub>2</sub>	36 mm
maximum torque	60 Nm
H <sub>1</sub>	50 - 65 mm
Length 1	50 mm

$F_{\max.}$	12.4 kN
Type	2
Type of product	Clamping hook