



Clamping hook with collar M16, Type: 3



Order data

Order number	370072 3
GTIN	2050001880017
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370079.

Technical description

H ₁	50 - 65 mm
F _{max.}	12 kN
Length 1	60 mm
Type	3
maximum torque	60 Nm

Thread M	M16
Height H ₂	36 mm
Type of product	Clamping hook