



Clamping hook with collar M16, Type: 4



Order data

Order number	370072 4
GTIN	2050001874559
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370079.

Technical description

Thread M	M16
F _{max.}	13.4 kN
Height H ₂	36 mm
maximum torque	60 Nm
Type	4

H ₁	65 - 80 mm
Length 1	40 mm
Type of product	Clamping hook