



## Clamping hook with collar M16, Type: 5



### Order data

Order number	370072 5
GTIN	2050001882813
Item class	37K

### Description

**Version:**

Entirely of hardened and tempered steel; burnished.

**Application:**

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

**Suitable for:**

Height element No. 370079.

### Technical description

Thread M	M16
F <sub>max.</sub>	12.4 kN
Height H <sub>2</sub>	36 mm
H <sub>1</sub>	65 - 80 mm
Type	5

maximum torque	60 Nm
Length 1	50 mm
Type of product	Clamping hook