



Clamping hook with collar M16, Type: 6



Order data

Order number	370072 6
GTIN	2050001880154
Item class	37K

Description

Version:

Entirely of hardened and tempered steel; burnished.

Application:

Screwed directly into a grid hole, no countersinking required.

For space-saving clamping of workpieces.

For space-saving clamping of workpieces.

Suitable for:

Height element No. 370079.

Technical description

$F_{max.}$	12 kN
Height H_2	36 mm
Type	6
Length 1	60 mm
H_1	65 - 80 mm

maximum torque	60 Nm
Thread M	M16
Type of product	Clamping hook