



Swing clamp, without handle, Type: 30R



Order data

| | |
|--------------|---------------|
| Order number | 370085 30R |
| GTIN | 2050001883094 |
| Item class | 37K |

Description

Version:

- **"One Touch" swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).**
- **Body of hardened and tempered steel; burnished.**
- **Even clamping force over the component.**
- **Removable handle, so few interference contours.**

Application:

- **For quickly clamping and releasing individual components.**
- **For light duty machining work.**

Note:

Screw-in handles with torque limitation available on request.

maximum clamping force: 800 N

max. hand force grip: 150 N

Technical description

| | |
|----------|---------|
| Height H | 57.5 mm |
|----------|---------|

| | |
|-------------------------------------|---------------------|
| Thread M | M6 |
| Dimension E | 18 mm |
| B ₁ | 14 mm |
| L ₂ | 15 mm |
| L ₁ | 32 mm |
| Type | 30R |
| Clamping height H ₁ min. | 31.4 mm |
| Clamping height H ₁ max. | 32.6 mm |
| maximum clamping force | 800 N |
| max. hand force grip | 150 N |
| B | 30 mm |
| L ₃ | 25 mm |
| Thread M ₁ | M4 |
| Type of product | Jig clamping system |