



Swing clamp, with handle, Type: 30R



Order data

Order number	370086 30R
GTIN	2050001883933
Item class	37K

Description

Version:

- **“One Touch” swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).**
- **Body of hardened and tempered steel; burnished.**
- **Even clamping force over the component.**
- **Removable handle, so few interference contours.**

Application:

- **For fast clamping / releasing of individual components.**
- **For light machining work.**

Note:

Screw-in handles with torque limitation available on request.
 maximum clamping force: 800 N
 max. hand force grip: 150 N

Technical description

Dimension E	18 mm
Thread M	M6
Height H	57.5 mm
L ₁	32 mm

Type	30R
L ₂	15 mm
B ₁	14 mm
Clamping height H ₁ min.	31.4 mm
Clamping height H ₁ max.	32.6 mm
maximum clamping force	800 N
max. hand force grip	150 N
B	30 mm
L ₃	25 mm
Thread M ₁	M4
Type of product	Jig clamping system