



## Swing clamp, with handle, Type: 40R



### Order data

Order number	370086 40R
GTIN	2050001877352
Item class	37K

### Description

#### Version:

- **“One Touch” swing clamp with axial clamping stroke (H1/H2) by lever movement (right/left).**
- **Body of hardened and tempered steel; burnished.**
- **Even clamping force over the component.**
- **Removable handle, so few interference contours.**

#### Application:

- **For fast clamping / releasing of individual components.**
- **For light machining work.**

#### Note:

Screw-in handles with torque limitation available on request.  
 maximum clamping force: 1200 N  
 max. hand force grip: 200 N

### Technical description

L <sub>1</sub>	40 mm
L <sub>2</sub>	20 mm
B <sub>1</sub>	16 mm

Height H	78.1 mm
Dimension E	25 mm
Type	40R
Thread M	M8
Clamping height H <sub>1</sub> min.	44.1 mm
Clamping height H <sub>1</sub> max.	45.9 mm
maximum clamping force	1200 N
max. hand force grip	200 N
B	40 mm
L <sub>3</sub>	32 mm
Thread M <sub>1</sub>	M6
Type of product	Jig clamping system