

**Location device, Type: DTECT120****Order data**

Order number	465570 DTECT120
GTIN	3165140780070
Item class	46T

Description**Version:**

Reliable location even of buried objects up to 120 mm deep. Three detection modes (plasterboard, metal, live cables) for different applications. Reliable detection of objects, giving a visual and acoustic signal. Point measurement enables location even on very small surfaces. Optical indication of direction for precise localisation of the object centre.

Application:

Detectable materials: Ferrous metals, non-ferrous metals, wooden frameworks, live cables.
Additionally detectable material: Plastic pipes filled with water.

Supplied with:

Li-ion battery, quick charger, L-Boxx

Technical description

Measuring range	120 mm
Detection depth steel	120 mm
Detection depth copper	120 mm
Detection depth live conductors	60 mm

Detection depth wood	38 mm
Accuracy	±10 mm
Weight	490 g
Length	206 mm
Width	92 mm
Height	85 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Packaging	Modular case (L-Boxx)
Type of product	Location device