

**Laser distance meter, Type: GLM30****Order data**

Order number	465560 GLM30
GTIN	3165140735346
Item class	46T

**Description****Version:**

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof (IP 54). Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Simple laser distance measurement device for indoor use.

**Standard:**

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof (IP 54). Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Stand socket thread 1/4 inch. The integral 360° inclination sensor shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement. Create a digital floor plan, import existing floor plans, edit them and export the result together with simple building site dimensioning. Data transfer via Bluetooth®.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Includes protective case. With batteries 081551 LR3.

**Optional extras:**

Measuring stand No. 468558.

IP Index of Protection: IP 54

Measuring accuracy:  $\pm 2$  mm

Article no of the battery / rechargeable battery fitted: 081551 LR3  
 Range: 30 m  
 Addition/subtraction: yes  
 Power supply: 081551 LR3  
 Length: 105 mm

## Technical description

Power supply	081551 LR3
Addition/subtraction	yes
Weight	100 g
Height	24 mm
Width	41 mm
Measuring accuracy	±2 mm
Length	105 mm
Battery life (measurements)	5000
Range	30 m
IP Index of Protection	IP 54
Article no of the battery / rechargeable battery fitted	081551 LR3
Number of batteries contained	2
Power supply	Battery-powered
Laser class to IEC 825-1	2
Type of product	Distance meter

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
Photography tripod	468558