



**Super Knips® electronics side cutter, conductive grips with wire holder, kW,
overall length: 125mm**



Order data

Order number	726661 125
GTIN	4003773025191
Item class	73F

Description

Version:

Slim head with precision ground cutter, without chamfer. Handles with multi-component covering, with opening spring. **Suitable for ESDs.**

Material:

Special tool steel, burnished.

Technical description

overall length	125 mm
Head width	13.5 mm
Cutting capacity medium-hard steel wire	0.2 - 1.2 mm
Cutter length	9 mm
Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Special quality tool steel, oil-hardened
Standard	DIN ISO 9654
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Surface	black burnished
Product name attribute	kW
with return spring	yes
with wire holder	yes
Type of product	Cutting pliers