



Electronics side cutter Super Knips[®], kW, overall length: 125mm



Order data

Order number	726620 125
GTIN	4003773035404
Item class	73F

Description

Version:

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

Application:

Suitable even for cutting glass fibre cable (fibre optic cable).

Standard:

DIN ISO 9654

Material:

Special tool steel, burnished.

Technical description

Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
Head width	13.5 mm
Cutting capacity medium-hard steel wire	0.2 - 1.2 mm
Cutter length	9 mm
overall length	125 mm
Cutting chamfer	without bevel
Material	Special tool steel
Standard	DIN ISO 9654
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Surface	burnished
Product name attribute	kW
with return spring	yes
with wire holder	no
Type of product	Cutting pliers