



## Electronics side cutter Super Knips® with wire holder, SFW, overall length: 125Hmm



### Order data

Order number	726650 125H
GTIN	4003773065081
Item class	73F

### Description

#### Version:

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

#### Standard:

**DIN ISO 9654**

#### Material:

Special tool steel, burnished.

### Technical description

Cutting capacity medium-hard steel wire	0.2 - 1.2 mm
Cutting capacity hard wire up to Ø	0.2 - 0.6 mm
Cutting capacity copper wire up to Ø	0.2 - 1.6 mm
Head width	13.5 mm
Cutter length	9 mm
overall length	125 mm
Cutting chamfer	very fine bevel
Material	Special tool steel
Standard	DIN ISO 9654

Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Surface	burnished
Product name attribute	SFW
with return spring	yes
with wire holder	yes
Type of product	Cutting pliers