



Electronics side cutter Super Knips[®], conductive grips, kW, overall length: 125mm



Order data

| | |
|--------------|---------------|
| Order number | 726660 125 |
| GTIN | 4003773025184 |
| Item class | 73F |

Description

Version:

Slim head with precision ground cutter, without chamfer. Handles with multi-component covering, with opening spring. **Suitable for ESDs.**

Application:

Suitable even for cutting glass fibre cable (fibre optic cable).

Material:

Special tool steel, burnished.

Technical description

| | |
|---|--|
| overall length | 125 mm |
| Head width | 13.5 mm |
| Cutter length | 9 mm |
| Cutting capacity copper wire up to Ø | 0.2 - 1.6 mm |
| Cutting capacity medium-hard steel wire | 0.2 - 1.2 mm |
| electrostatic characteristic | EGB/ESD |
| Cutting chamfer | without bevel |
| Material | Special quality tool steel, oil-hardened |
| Standard | DIN ISO 9654 |

| | |
|------------------------|---|
| Handle | Multi-component covering |
| Manufacturing process | Cutting edges induction hardened (approx. 64 HRC) |
| Surface | black burnished |
| Product name attribute | kW |
| with return spring | yes |
| with wire holder | no |
| Type of product | Cutting pliers |