




## Weldon element with compensation, short, For nominal $\varnothing$ d: 9mm



### Order data

Order number	335720 9
GTIN	4045197801517
Item class	32P

### Description

#### Version:

Plain toolholder, hardened and ground with **quick-release coupling**. Internal square to take taps and transmit the torque. Clamping mechanism prevents the tap being pulled out. Tensile/compression compensation each of 0.2 mm by means of compensation element. Clamping of the Weldon element either by means of the drive flats or the compensation element.

#### Advantage:

- **Attractively priced solution.**
- **Sturdy, slim version.**
- **Variation in the clamping and overhang lengths.**

#### Application:

To take taps and others in a Weldon arbor.

#### Optional extras:

Compensation element No. 335730.

#### Note:

Minimum compensation function **only** in combination with No. 300415 and 335730. The standard Weldon chuck permits only rigid clamping, see No. 335740.

### Technical description

External $\varnothing$ D	18 mm
Adjustment travel V	10 mm
Clamping range d	9 mm
Overhang A	41.5 mm

Overall length L	48 mm
Type of product	Tapping head

---

## Accessories

Compensation element Clamping range d 7-10 mm	335730 7-10
---	-------------